



Locking Devices, Industrial, Flanged Inlet, 30A 277V AC, 2-Pole 3-Wire Grounding, L7-30P, Screw Terminal, White

By Bryant
Catalog # 70730MB

Locking Devices, Industrial, Flanged Inlet, 30A 277V AC, 2-Pole 3-Wire Grounding, L7-30P, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L7-30P

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3500V
Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	277V AC
Connectivity	Screw Terminals
Voltage Rating	277 VAC



Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	30A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786690264

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)