



## Locking Devices, Industrial, Flush Receptacle, 20A125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Black

By Bryant  
Catalog # [71420FR](#)

Locking Devices, Industrial, Flush Receptacle, 20A125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screw Terminal, Black



### Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

### Application

Extra Heavy Duty Industrial Specification Grade

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	L14-20R

### Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

### Current

Current/Amperage Rating	20 Amp
Description	

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125/250V AC
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	125/250 VAC

### Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.14 in
Dimensions	3.28 in x 1.70 in x 1.14 in

### General

Style	Single Receptacle
Item Type	20A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting Receptacle
Type	Receptacle
Material	Composite
UPC	781786695139

### Logistics

Carton Quantity	10
Pallet Quantity	2340

### Product Assets

[Catalog \[English\]](#)