



Locking Devices, Industrial, Flanged Inlet,
20A 3-Phase Wye 347/600V AC, 4-Pole 5-
Wire Grounding, L20-20P, Screw Terminal,
White

By Bryant
Catalog # 72020MB

Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Wye
347/600V AC, 4-Pole 5-Wire Grounding, L20-20P, Screw
Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L20-20P

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Dielectric Strength	Withstands 3000V Minimum
Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 277/480V AC
Connectivity	Screw Terminals
Voltage Rating	3 Phase Y 277/480 VAC



Dimensions

Display Size	Standard Sized Product
Length	3.06 in
Width	3.06 in
Height	2.03 in
Dimensions	3.06 in x 3.06 in x 2.03 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	20A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786700260

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)