



Locking Devices, Industrial, Flush
Receptacle, 20A 250V, 2-Pole 2-Wire Non-
Grounding, L2-20R, Screw Terminal, Gray

By Bryant
Catalog # 7210B

Locking Devices, Industrial, Flush Receptacle, 20A 250V,2-Pole 2-
Wire Non-Grounding, L2-20R, Screw Terminal, Gray

Features

- Flush Receptacle
- 20A 250V
- 2-Pole 2-Wire Non-Grounding
- L2-20R
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	L2-20R

Conductor

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating Description	20 Amp
Current Rating	20 A



Amperage Rating	20 A
Voltage Rating Description	250V
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Height	1.00 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	20A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786627765

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)



A Hubbell brand