



Locking Devices, Industrial, Flanged Inlet,
20A 3-Phase Delta 480V AC, 3-Pole 4-Wire
Grounding, L16-20P, Screw Terminal, With
Weatherproof Cover

By Bryant
Catalog # 71620MBWP

Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta
480V AC, 3-Pole 4-Wire Grounding, L16-20P, Screw Terminal,
White, With Weatherproof Cover

Features

- Flanged Inlet
- 20A 3-Phase Delta 480V AC
- 3-Pole 4-Wire Grounding
- L16-20P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	Yes
Nema Rating	L16-20P

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase 480 VAC
Connectivity	Screw Terminals
Voltage Rating	3 Phase 480 VAC



Dimensions

Display Size	Standard Sized Product
Length	2.88 in
Width	2.88 in
Height	2.02 in
Dimensions	2.88 in x 2.88 in x 2.02 in

General

OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Color	White
Item Type	20A Weather Protective Power Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786696877

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)