



Locking Devices, Isolated Ground,
Industrial, Flush Receptacle, 30A 3-Phase
Wye 120/208V AC, 4-Pole 5-Wire
Grounding, L21-30R, Screw Terminal,
Orange

By Bryant
Catalog # 72130IG



Locking Devices, Isolated Ground, Industrial, Flush Receptacle,
30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-
30R, Screw Terminal, Orange

Features

- Limits electrical noise on the equipment grounding circuit by providing two grounding paths for the installation
- Nylon deep face design
- Triple-wipe brass line contacts
- Ground contacts and ground termination
- Nickel and brass plated wrap-around steel yoke

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L21-30R

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	30 Amp
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase Y 120/208V AC

Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	120/208 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.70 in
Height	1.24 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

Series	Locking
OEM Brand Name	Hubbell Bryant
Style	Isolated Ground
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Single Receptacle
Material	Composite
UPC	781786701441

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)