



Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black

By Bryant
Catalog # [72020FR](#)



Locking Devices, Industrial, Flush Nylon Receptacle, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L20-20R, Screw Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	72020FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786700239

Dimensions

Dimensions 3.28 in x 1.70 in x 1.24 in

Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Three Phase
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L20-20R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 72020FR Specification Sheet French](#)
[Specifications - 72020FR Specification Sheet English](#)

