



Locking Devices, Industrial, Flanged
Receptacle, 20A 3-Phase Wye 277/480V
AC, 4-Pole 5-Wire Grounding, L22-20R,
Screw Terminal, White

By Bryant
Catalog # 72220ER

Locking Devices, Industrial, Flanged Receptacle, 20A 3-Phase
Wye 277/480V AC, 4-Pole 5-Wire Grounding, L22-20R, Screw
Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L22-20R

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 277/480V AC
Phase	Three Phase



Connectivity	Terminal Screws
Voltage Rating	3 Phase Y 277/480 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.06 in
Width	3.06 in
Height	2.03 in
Dimensions	3.06 in x 3.06 in x 2.03 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	20A Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Flanged Receptacle
Material	Composite
UPC	781786701809

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)