



Locking Devices, Industrial, Flush
Receptacle, 20A 250V, 3-Pole 4-Wire
Grounding, Non-NEMA, Screw Terminal,
Black

By Bryant
Catalog # 7410G

Locking Devices, Industrial, Flush Receptacle, 20A 250V, 3-Pole
4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Flush Receptacle
- 20A 250V
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	Non-NEMA

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250V AC



Phase	Three Phase
Connectivity	Terminal Screws
Voltage Rating	250 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.71 in
Height	1.14 in
Dimensions	3.28 in x 1.71 in x 1.14 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	20A Single Receptacle-For Replacement Use
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786628335

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)