



Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1P, Screw Terminal, Black

By Bryant
Catalog # 7466N

Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1P, Screw Terminal, Black

Features

- Industrial
- Flanged Inlet
- 15A 125V
- 2-Pole 2-Wire Non Grounding
- ML-1P

Application

Extra Heavy Duty Industrial

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-1P

Conductor

Number Of Wires	2-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125V
Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating Description	15 Amp
Current Rating	15 A
Voltage Rating	125 V



Connectivity	Screw Terminals
Dimensions	
Length	1.63 in
Display Size	Midget Locking
Height	1.28 in
Width	1.38 in
Dimensions	1.63 in x 1.38 in x 1.28 in

General

Color	White
Style	Non-Grounding
OEM Brand Name	Hubbell Bryant
UPC	781786638518
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Insulation	Insulated Body
Item Type	15A Midget Flanged Inlet
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	- Maximum Continuous: 75° C - Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)