



Locking Devices, Industrial, Flush
Receptacle, 20A 3-Phase Wye 347/600V AC,
4-Pole 5-Wire Grounding, L23-20R, Screw
Terminal, Black

By Bryant
Catalog # 72320FR

Locking Devices, Industrial, Flush Receptacle, 20A 3-Phase Wye
347/600V AC, 4-Pole 5-Wire Grounding, L23-20R, Screw Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L23-20R

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	4-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 347/600V AC



Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Voltage Rating	3 Phase Y 347/600 VAC
Connectivity	Terminal Screws
Phase	Three Phase

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Height	1.24 in
Width	1.70 in
Dimensions	3.28 in x 1.70 in x 1.24 in

General

Style	Single Receptacle
OEM Brand Name	Hubbell Bryant
UPC	781786702639
Type	Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	20A Single Nylon Receptacle
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)