



Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1R, Screw Terminal, Black

By Bryant
Catalog # 7468N

Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1R, Screw Terminal, Black

Features

- Industrial
- Flanged Receptacle
- 15A 125V
- 2-Pole 2-Wire Non Grounding
- ML-1R

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	ML-1R

Conductor

Number Of Wires	2-Wire
Wire Size	#18 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125V
Current/Amperage Rating Description	15 Amp



Current Rating	15 A
Voltage Rating	125 V
Connectivity	Terminal Screws
Phase	Single Phase

Dimensions

Length	1.63 in
Display Size	Midget Locking
Height	1.18 in
Width	1.38 in
Dimensions	1.63 in x 1.38 in x 1.18 in

General

Style	Non-Grounding
OEM Brand Name	Hubbell Bryant
UPC	781786638525
Type	Flanged Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	15A Midget Flanged Receptacle
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)