



Locking Devices, Industrial, Female
Connector Body, 20A 3-Phase Wye 347/600V
AC, 4-Pole 5-Wire Grounding, L23-20R,
Screw Terminal, Black and White

By Bryant
Catalog # 72320NC

Locking Devices, Industrial, Female Connector Body, 20A 3-Phase Wye 347/600V AC, 4-Pole 5-Wire Grounding, L23-20R, Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L23-20R

Conductor

Number Of Conductors	5-Wire Grounding
Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	4-Pole
Conductor Range	#14 AWG to #12 AWG

Current

Amperage Rating	20 A
Voltage Rating Description	3 Phase Y 347/600V AC
Current/Amperage Rating	20 Amp
Description	
Current Rating	20 A
Voltage Rating	3 Phase Y 347/600 VAC



Connectivity

Screw Terminals

Dimensions

Length	2.13 in
Display Size	Standard Sized Product
Height	3.90 in
Width	2.13 in
Dimensions	2.13 in x 2.13 in x 3.90 in

General

Color	Black, White
Style	Internal Cord Clamp
OEM Brand Name	Hubbell Bryant
UPC	781786702691
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	20A Triple Gripper Nylon Connector
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)