



Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White

By Bryant
Catalog # 7523

Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White

Features

- Flanged Inlet
- 15A 125V
- 2-Pole 2-Wire Non-Grounding
- L1-15P
- Screw Terminal

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Nema Rating	L1-15P

Conductor

Number Of Wires	2-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	15 Amp
Description	
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125V
Connectivity	Screw Terminals



Voltage Rating	125 V
Dimensions	
Display Size	Standard Sized Product
Length	2.56 in
Width	2.19 in
Height	1.78 in
Dimensions	2.56 in x 2.19 in x 1.78 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	15A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786629103

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)