

Locking Devices  
 15A, 125V, 2 Pole, 3 Wire Grounding  
 Elastogrip® Connector



**Features**

- Integral weatherproofing shroud seals connection between plug and connector
- Nylon compression nut keeps water and dust from getting into the body around the cord



**Ordering Information**

Description	Cord Diameter	UPC	Catalog Number
Elastogrip® Connector, yellow elastomer, water/dust tight	.300"-.655" (7.6-16.6)	781786378322	<b>BRY25W47</b>

**Listings**

Listed to UL 498  
 Fed.Spec. W-C-596  
 Certified to CSA C22.2 No.42

**Specifications**

Terminal Retainer	Clear polycarbonate
Strain Relief Nut	Nylon
Contacts	Brass
Terminal Screws	Brass
Assembly Screws	Steel, zinc plated


**Performance**

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 2,000V minimum

<b>Mechanical</b>	
Terminal Accommodation	#18 AWG- #10 AWG stranded copper wire only.

Terminal Identification	Terminals identified in accordance with UL 498
-------------------------	--

<b>Environmental</b>	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



**Accessories**

Plug	HBL24W47
------	----------

**Resources**

Customer Use Drawing  
 eCatalog