



8300HBW

By Bryant
Catalog # [8300HBW](#)

Straight Blade Devices, Receptacles, Duplex, Heavy Duty,
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Nylon, White

Features

- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hospital Grade

Performance

Electrical: Current Interrupting- Certified for current interrupting at full rated current, Electrical: Dielectric Voltage- Withstands 2,000V minimum, Mechanical: Product Identification Ratings are a permanent part of the device, Environmental: Flammability- UL 94V-2, Environmental: Operating Temperature- Maximum continuous 75°C, minimum -40°C (w/o impact)

Specifications

Nema Rating	5-20R
Industry Standard(s)	• Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186

Conductor

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V



Current Rating	20 A
Voltage Rating	125 V
Wattage	2500 W
Connectivity	Back and Side Wired
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.2 lb.
Height	1.1 in
Width	1.32 in
Dimensions	3.28 in x 1.32 in x 1.1 in

General

Color	White
Style	Smooth Face
Series	Hospital Grade
UPC	781786147171
Type	Standard Duplex
Material - Mounting Hardware	Screw Mounting
Item Type	Smooth Face
Material	Nylon

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

[Catalog \[English\]](#)