



Locking Devices, Flanged Inlet, 20A 250V, 2- Pole2-Wire Non-Grounding, Non-NEMA, Black

By Bryant
Catalog # 8808MB

Locking Devices, Flanged Inlet, 20A 250V, 2- Pole2-Wire Non-Grounding, Non-NEMA, Black

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Nema Rating	L2-20P

Conductor

Number Of Wires	2-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating Description	20 Amp
Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	250V
Connectivity	Screw Terminals



Voltage Rating	250 V
----------------	-------

Dimensions

Display Size	Standard Sized Product
Length	2.56 in
Width	2.56 in
Height	1.72 in
Dimensions	2.56 in x 2.56 in x 1.72 in

General

OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Color	White
Item Type	20A Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware Type	Screw Mounting Flanged Inlet
Material	Composite
UPC	781786630789

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)