


IEC Pin and Sleeve

20 A, 3 Phase 600 VAC, 3-POLE, 4-WIRE

Angled Receptacle



- Features
- IP67 environmental ratings
 - Impact and corrosion resistant insulated non-metallic housing
 - Sequential contact engagement to prevent a momentary over-voltage
 - Color coded housings provide quick identification of mating devices



Ordering Information				
Description	Series	Color	UPC Number	Catalog Number
Heavy Duty Products, IEC Pin and Sleeve	Watertight IP67	Black	781786783041	BRY420AR5W

Complementary Products	
Complementary Products	Adapter Plate, Back Box

Listings
All constructions are UL Listed & cUL Listed
File E14632
UL1686 Standard for Pin & Sleeve Configurations
CE

Specifications	
Application	High Ampacity Connections
Connection	Pressure Screw Terminal
Wire Size	#14AWG to #12AWG
Material	PBT
Mounting	Screw Mount

Performance	
Electrical	
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V AC RMS
Mechanical	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are marked on device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
Environmental	
Flammability	HB
Ingress Protection	IP67
Moisture Resistance	IEC 60309-1
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.

Online Resources

Customer Sales Drawings

eCatalog

