



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, Nylon, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30P, Single Pack

By Bryant
Catalog # 9432ANPB

Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Angled, Nylon, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30P, Black, Single Pack

Features

- Tailored for EV Charging: This receptacle is purpose-built to cater to the specific needs of EV charging. It incorporates features and specifications that are optimized for the safe and efficient charging of electric vehicles.
- Industrial-Grade Construction: This EV receptacle boasts a robust and durable construction. It is engineered using high quality materials that can withstand demanding environments, ensuring long-lasting performance and reliability.
- Secure Connection: The terminal box protects against loose or disconnected wires while providing a stable and durable enclosure, safeguarding the wires from external elements and potential damage. With a clamping mechanism, the receptacle ensures tight and efficient termination, minimizing the risk of power loss or overheating.
- Contact Force & Durability: The thick wall terminal box delivers a 50% greater contact force on plug blades, ensuring a secure and reliable connection, minimizing power interruptions, and fluctuations for a stable power supply. The receptacle is designed for durability, withstanding heavy usage and frequent insertions and removals without compromising performance.
- Fast & Efficient Charging: The receptacle features a 3-pole, 4-wire grounding configuration, providing a secure electrical connection for EV charging. This configuration ensures proper grounding, minimizing the risk of electrical faults and ensuring a safe charging process. With a 50A, 125/250V rating, it delivers high-power charging capabilities, enabling faster charging times for EVs.
- Effortless Installation: Designed with user convenience in mind, this EV Charging Receptacle offers a hassle-free installation process. It features a straightforward wiring mechanism, allowing both professional electricians and DIY enthusiasts to easily set up the charging infrastructure.

Application

Heavy Duty

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes



Nema Rating	14-30P
Conductor	
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG
Number Of Poles	3-Pole
Configuration	
Cord Type	All Portable
Current	
Amperage Rating	30 A
Voltage Rating Description	125/250 V
Current Rating	30 A
Voltage Rating	125/250 V
Wattage	7500
Connectivity	Pressure Terminal Screws
Phase	Single Phase
Current / Amperage Rating	30 A
Dimensions	
Display Size	Standard Sized
Weight	0.75 lb.
General	
Color	Black and White
Style	Heavy Duty
Series	Industrial
OEM Brand Name	Hubbell Bryant
UPC	781786676107
Type	Plug
Material - Mounting Hardware	Cord Mounted
Item Type	Standard
Material	Composite
Logistics	
Pallet Quantity	1200
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)



A Hubbell brand