



TECH-SPEC, Motor Disconnect Switch, 3 Pole, 200A 600V AC, NEMA 4X,12 Stainless Steel

By Bryant
Catalog # BRYDS20SS



TECH-SPEC, 200A stainless steel Enclosed Motor Disconnect

Features

- UL 98 HP rated motor disconnect
- Formed in corrosion resistant stainless steel
- OSHA Compliant Lockout/Tagout Handle
- Type 4X, 12
- Highly Visible Red Rotary Handle
- Cover cannot be removed with switch in "on position"

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL 98
Environmental Conditions	Type 4, 12
Nema Rating	4X, 12

Conductor

Number Of Poles	3
-----------------	---

Configuration

Mounting Method	External
Contact Configuration	Two Position

Current

Phase	3-Phase
Dielectric Strength	Withstands 3000V AC minimum
Contact Rating	200A
Amperage Rating	200 A
Wattage	120000 W
Voltage Rating	600 V

Dimensions

Size	20 in x 15.8 x 11.45 in
Width	15.8 in
Weight	49 lb.

General

Type	Disconnect Switches
Enclosure Type	Stainless Steel
Material	304 Stainless Steel
UPC	781786967151
Style	Heavy Duty
Mounting Type	External mounting feet

Operational

Operating Cycles	Minimum 10,000
Operating Temperature	• Maximum Continuous 75 °C • Minimum Continuous -40°C without impact
Action	Rotary