



TECH-SPEC, Motor Disconnect Switch, 3 Pole, 30A 600V AC, NEMA 4X,12 Stainless Steel Enclosure, 1 NO & NC Aux Contact

By Bryant
Catalog # BRYDS30SSAC

TECH-SPEC, 30A stainless steel Enclosed Motor Disconnect w/ Auxiliary Contact



Features

- UL 508 / UL 60947-4-1 HP rated motor disconnect
- Formed in nonporous 304 stainless steel
- Type 4X,12K water ingress protection
- Highly visible yellow handle which meets OSHA Lockout/Tagout capabilities
- Accepts up to 2 Auxiliary contacts
- Cover cannot be removed with switch in "on position"
- Replacement cover and switch available

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL60947-1 CSA C22.2, UL60947-4-1, UL50, UL50E, UL508, UL746C
Environmental Conditions	NEMA 4X, IP69K
Nema Rating	4X, 12

Conductor

Number Of Poles	3
-----------------	---

Configuration

Mounting Method	External
Contact Configuration	Two Position

Current

Phase	3-Phase
Dielectric Strength	Withstands 3000V AC minimum
Contact Rating	30A
Amperage Rating	30 A
Wattage	18000 W
Voltage Rating	600 V

Dimensions

Size	7 in x 4.9 in x 5.39
Width	4.9 in
Weight	4.903 lb.

General

Type	Disconnect Switches
Enclosure Type	Stainless Steel
Material	304 Stainless Steel
UPC	781786967014
Style	Heavy Duty
Mounting Type	External mounting feet

Operational

Operating Cycles	Minimum 10,000
Operating Temperature	• Maximum Continuous 75 °C • Minimum Continuous -40°C without impact
Action	Rotary