



Locking Devices, Locking Devices,
Industrial, Female Connector Body, 50A
250V, 2-Pole 3-Wire Grounding, Non-
NEMA, Screw Terminal, Black and White

By Bryant
Catalog # [CS8264](#)

Locking Devices, Locking Devices, Industrial, Female Connector
Body, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA,Screw
Terminal, Black and White

Features

- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength
- Oversized contacts minimize operating temperature

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#6 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	250 VAC
Connectivity	Pressure Terminal Screws
Voltage Rating	250 VAC



Dimensions

Display Size	Standard Sized Product
Length	6.50 in
Width	2.56 in
Height	2.56 in
Dimensions	6.50 in x 2.56 in x 2.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Heavy Duty Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786831124

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)