



Locking Devices, Industrial, Flanged Inlet,
50A Phase Delta 480V AC, 3-Pole 4-Wire
Grounding, Non-NEMA, Screw Terminal,
Steel

By Bryant
Catalog # [CS8175A](#)

Locking Devices, Industrial, Flanged Inlet, 50A Phase Delta 480V
AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No


Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	3 Phase 480V AC
Connectivity	Pressure Terminal Screws
Voltage Rating	3 Phase 480 VAC

Dimensions



Display Size	Standard Sized Product
Length	2.77 in
Width	3.50 in
Height	3.50 in
Dimensions	2.77 in x 3.50 in x 3.50 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Metallic
Item Type	50A Male Flanged Inlet
Insulation	Insulated Body
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Composite
UPC	781786253148

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)