



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, FSL3R, Screw Terminal, Black

By Bryant
Catalog # [FSL3FR](#)



Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, FSL3R, Screw Terminal, Black

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	FSL3-R

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	30 Amp 400 Hz
Description	

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	3 Phase Delta 120V
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	3 Phase Delta 120 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.71 in
Height	1.14 in
Dimensions	3.28 in x 1.71 in x 1.14 in

General

OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Item Type	30A Single Nylon Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786638280

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)