




Power Protection Products, GFCI Circuit Breakers, Industrial, Single Pole, 40A 120V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFMDCB120401P](#)

Power Protection Products, GFCI Circuit Breakers, Industrial, Single Pole, 40A 120V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black



Features

- Industrial
- Single Pole
- 40A 120V AC
- GFCI Circuit Breaker Sensing Modules
- 4-6 mA Trip Level

Application

Heavy Duty Industrial Commercial

Specifications

Environmental Conditions	NEMA 4X with Supplied Gasket
EU RoHS Indicator	No

Conductor

Wire Size	Terminal Screws
Number Of Poles	None

Current

Current Rating	40 A
Amperage Rating	40 A
Frequency Rating	80% of Full Rating Continuous
Voltage Rating Description	120 VAC
Phase	60Hz
Current / Amperage Rating	40 A
Connectivity	None
Trip Type	Standard
Trip Range	.025 Seconds in

Interrupt Rating	40 A
Voltage Rating	120 VAC

Dimensions

Width	0.73 in
-------	---------

General

Enclosure Type	Toggle
Series	Industrial
OEM Brand Name	Hubbell Bryant
Frame	Single Phase
Style	1 Pole
Color	Black
Item Type	Circuit Breaker
Type	Circuit Breaker
Material	Composite
UPC	781786450202

Logistics

Carton Quantity	36
-----------------	----

Operational

Timing Response	1-Pole
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)