



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [SP53IGIA](#)



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Ivory

Features

- Isolated Ground
- 20A 125V
- 2- Pole 3-Wire Grounding
- 5-20R
- Ivory

Application

IG Duplex with Light and Alarm

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-20R
Current	
Current Rating	20 A
Amperage Rating	20 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size Standard

General

Series	Specification Grade
OEM Brand Name	Hubbell Bryant
Outlet Style	Straight Blade Isolated Ground
Color	Ivory
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	Duplex Receptacle
Material	Composite
UPC	781786139183

Logistics

Carton Quantity 10

Operational

Response Time	5
Indicator(s) Type	LED and Audible Alarm
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)