



Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray

By Bryant
Catalog # [SP83GYA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray



Features

- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R
- Gray

Application

Duplex with Light and Alarm

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-20R

Current

Current Rating	20 A
Amperage Rating	20 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard
General	
Series	Hospital Grade
OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade
Style	Isolated Ground
Color	Gray
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	Duplex Receptacle
Material	Composite
UPC	781786139299
Logistics	
Carton Quantity	10
Operational	
Response Time	5
Indicator(s) Type	LED and Audible Alarm
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)