



Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White

By Bryant
Catalog # [SP83IGWA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, White



Features

- Isolated Ground
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R
- White

Application

IG Duplex with Light and Alarm

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-20R

Current

Frequency Rating	60 Hz
Amperage Rating	20 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V
Connectivity	Terminal Screws
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Display Size	Standard
General	
Color	White
Style	Isolated Ground
Outlet	Straight Blade
Series	Hospital Grade
OEM Brand Name	Hubbell Bryant
UPC	781786154643
Type	Duplex Receptacle
Material - Mounting Hardware	Mounting Screws
Item Type	Surge Protection Receptacles
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Response Time	5
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Indicator(s) Type	LED and Audible Alarm

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)