

# HUBBELL Premise Wiring

## PlugTrak, Aluminum, Tamper Resistant, 20A Circuit, 6 Receptacle, 3' Aluminum



By Hubbell Premise Wiring  
Catalog # [HBLALU24GB306](#)

PlugTrak, Aluminum, Tamper Resistant, 20A Circuit, 6  
Receptacle, 3' Aluminum

### Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

### Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,  
Mechanical - Wire - #12 AWG Stranded Copper

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul>
EU RoHS Indicator	Contact Manufacturer

### Conductor

Wire Size	#12 AWG THHN
-----------	--------------

### Configuration

Number Of Receptacles	6
-----------------------	---

### Current

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

### Dimensions

Length	3 ft
--------	------

### General

Item Type	Aluminum Pre-Wired PlugTrak
Type	Single Circuit
Series	Aluminum
Specifications	<ul style="list-style-type: none"><li>• Circuits - Single</li><li>• Material - Anodized Aluminum</li><li>• Number of Receptacles - 6 Singles</li><li>• PlugTrak Length - 3 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Receptacle Spacing - 6 Inch</li></ul>
UPC	783585113333
Style	Standard

### Logistics

Carton Quantity	2
-----------------	---

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)