

Non-Metallic Raceway, BaseTrak Series, 3-Gang, Full Capacity Raised Box

By Hubbell Premise Wiring
Catalog # [PB3FCIB3G](#)

Non-Metallic Raceway BaseTrak, 3-Gang, Full Capacity Raised Box

Features

- Reduces inventory requirements
- Eliminates need to order three separate boxes
- Boxes available in low, standard and deep profiles

Performance


Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Contact Manufacturer

Configuration

Number of Gang(s)	3-Gang
-------------------	--------



General

Item Type	PB3 BaseTrak Series
Type	Boxes
Series	PB3
Specifications	• Crush Resistance - 300 lbs. • Impact Resistance - 5 ft. lbs. • Material - UV Stabilized PVC
UPC	783585090962
Style	Full Capacity
Color	Office White

Logistics

Carton Quantity	12
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)