

Non-Metallic Raceway, BaseTrak, 2 or 3 Channel, 2-Gang, Flush, Inline Box

By Hubbell Premise Wiring
Catalog # [PB2IND2G](#)

Non-Metallic Raceway BaseTrak, 2 or 3 Channel, Double, Flush, Inline Box

Features

- Reduces inventory requirements
- Eliminates need to order three separate boxes
- Boxes available in low, standard and deep profiles

Application

2-Gang Inline Device Box

Performance

Environmental - Flame Rating - UL94V-0, Environmental - Temperature Range - -25.6° to 158° F


Specifications

Industry Standard(s)	UL 5A
EU RoHS Indicator	Contact Manufacturer

Configuration

Number of Gang(s)	2-Gang
-------------------	--------

General



Item Type	PB2 BaseTrak Series
Sub Brand	Non-Metallic Raceway
Type	Boxes
Series	PB2
Cover Type	Removable
Specifications	• Crush Resistance - 300 lbs. • Impact Resistance - 5 ft. lbs. • Material - UV Stabilized PVC
UPC	783585310114
Style	In-Line
Color	Office White

Logistics

Carton Quantity	10
Pallet Quantity	320

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)