

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes

2-Gang Recessed

HUBBELL

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- Stamped steel construction, exterior coated with fusion bonded epoxy paint for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	Catalog Number	UPC Number
Round	On/ Above Grade	CFB2G25RCRE	783585695198

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	16 gauge galvanized steel
Box Finish	Green corrosion resistant epoxy paint
Top Mouning Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) 47.5 IN³ [778 CM³]

Performance

Height

3.25" [82.6mm]

Length

16.27" [413.3mm]

Trade Size Knock-Outs: Ends

(2) ½", ¾", 1"

Width

7.32" [185.9mm]



Accessories

3/4" Prepour stackable ring extensions	CFB6RCVRR075
3-Cubes, Single Circuit	PWFBMP3R

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions