

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes

4-Gang Recessed



Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- Stamped steel construction, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	Catalog Number	UPC Number
Round	Above Grade	CFB4G25RE	783585695273



Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	16 gauge galvanized steel
Box Finish	Natural
Top Mouning Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(4) 41.5 IN³ [680 CM³]

Performance

Height

3.25"[82.6mm]

Length

14.57" [370.1mm]

Trade Size Knock-Outs: Ends

(4) ½", ¾", 1"

Width

11.20" [284.5mm]

Accessories

3/4" Prepour stackable ring extensions	CFB6RCVRR075
3-Cubes, Single Circuit	PWFBMP3R

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

