

OptiChannel

Indoor/Outdoor Tight Buffer Cable

Riser

HUBBELL

- Features
- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
 - E-Z Strip Buffer For Contractor-Friendly Termination
 - Compact Cable Diameter Reduces Pathway Congestion
 - Premium Fiber For Enhanced Optical Performance

Ordering Information

Description	Fiber	Catalog Number	UPC Number
2 strand, OM1, MM, I/O Tight Buffer Riser, Indoor/Outdoor Tight Buffer - Black	OM1 Multimode	HFCD14002R6BK	662620555591

Listings

ANSI/ICEA S-83-596

TIA-568.3-D

NFPA-262/UL910/CSA FT-6

Telcordia GR-409 and GR-20

Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.17 (4.4)
Cable Weight (lb/kft)	12
Construction	Single Unit, Aramid Strength Member
Armor	None

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

150

Maximum Operating Temperature

-4°F to +185°F (-20°C to +85°C)

Minimum Bend Radius, In-Service in (cm)

1.73 (4.4)



Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

Online Resources

eCatalog