

Straight Blade Devices  
15A, 125V, 2 Pole, 3 Wire Grounding  
Commercial Specification Grade Duplex  
Receptacles for Controlled Applicatoins

HUBBELL

Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Half-Controlled receptacle with one face marked and the circuit tab removed
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

Ordering Information

| Description                       | Device Color | UPC          | Catalog Number |
|-----------------------------------|--------------|--------------|----------------|
| Smooth face, back and side wired. | Brown        | 783585551029 | BR15C1         |

Listings

UL Listed to UL498 File No. E2186  
CSA Certified 22.2, No. 42  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

Specifications

|                                 |                                    |
|---------------------------------|------------------------------------|
| Wire Clamp                      | .062 in. (1.6) Nickel plated steel |
| Face                            | Nylon                              |
| Base                            | Nylon                              |
| Power Contacts                  | .030 in. (.8) Brass                |
| Ground Contacts                 | Brass                              |
| Terminal Screws                 | Plated steel                       |
| Mounting Strap                  | .040 in. (1) Galvanized steel      |
| Automatic Self-grounding Staple | Stainless steel                    |
| Mounting Screws                 | Galvanized Steel                   |

Performance

Electrical


|                      |                                                          |
|----------------------|----------------------------------------------------------|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

Mechanical

|                         |                                                        |
|-------------------------|--------------------------------------------------------|
| Product Identification  | Ratings are a permanent part of the device             |
| Terminal Accommodation  | #14-#10 AWG stranded or solid copper wire only         |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

Environmental

|                        |                                                     |
|------------------------|-----------------------------------------------------|
| Flammability           | UL 94 V-2                                           |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



Online Resources

[eCatalog](#)