

Straight Blade Devices, Receptacles, Duplex, 1/2 Load Controlled, 15A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, Red

By Hubbell Wiring Device-Kellems
Catalog # [BR15C1R](#)

Straight Blade Devices, Receptacles, Duplex, 1/2 Load Controlled, 15A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, Red



Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Half-Controlled receptacle with one face marked and the circuit tab removed
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

Application

Commercial Specification Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified 22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-15R |

Conductor

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #10 AWG |
| Number Of Poles | 2-Pole |

Current

| | |
|---------------------------|---------------------------|
| Dielectric Strength | Withstands 2,000V minimum |
| Current / Amperage Rating | 15 A |

| | |
|----------------------------|---------------------|
| Connectivity | Back and Side Wired |
| Current Rating | 15 A |
| Amperage Rating | 15 A |
| Voltage Rating Description | 125 V |
| Wattage | 1875 W |
| Voltage Rating | 125 V |

Dimensions

| | |
|--------------|-----------------------------|
| Display Size | Standard Sized Product |
| Width | 1.57 in |
| Height | 1.07 in |
| Length | 3.28 in |
| Dimensions | 3.28 in x 1.57 in x 1.07 in |

General

| | |
|----------------|---|
| Item Type | Traditional Duplex |
| Type | One Controlled Face, Split Circuit |
| Series | Controlled |
| Material | Nylon |
| Specifications | <ul style="list-style-type: none"> • Automatic Self-grounding Staple - Stainless steel • Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Galvanized Steel • Mounting Strap - .040 in. (1) Galvanized steel • Power Contacts - .030 in. (.8) Brass • Terminal Screws - Plated steel • Wire Clamp - .062 in. (1.6) Nickel plated steel |
| Style | Smooth Face |
| Color | Red |

Operational

| | |
|-----------------------|--|
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Horsepower - Maximum | 0.5 |

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
WDK-BR15C1R-SPEC-EN | REV 1/2026