

Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [8200IVTRA](#)

Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Ivory

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

EU RoHS Indicator	Contact Manufacturer
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 2,000V minimum
---------------------	---------------------------



Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Wattage	1875 W
Voltage Rating	125 VAC

Dimensions

Length	3.28 in
Width	1.57 in
Weight	0.2 lb.
Height	1.15 in
Dimensions	3.28 in x 1.57 in x 1.15 in

General

Series	Hubbell-Pro
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Smooth Face
Color	Ivory
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Nylon
Specifications	• Automatic Self-grounding Staple - Stainless steel • Base - PBT • Clamping Plate - Plated steel • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Galvalized steel • Power Contacts - Brass
UPC	783585542140

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)

