

## Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [8200LALTRA](#)

Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Light Almond



### Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

### Application

Hubbell-Pro Heavy Duty Hospital Grade

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### Specifications

|                      |   |
|----------------------|---|
| EU RoHS Indicator    | Contact Manufacturer  |
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul> |
| Nema Rating          | 5-15R   |

### Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |
| Number Of Poles | 2-Pole             |

### Current

|                     |                           |
|---------------------|---------------------------|
| Dielectric Strength | Withstands 2,000V minimum |
| Current Rating      | 15 A                      |

|                            |                     |
|----------------------------|---------------------|
| Amperage Rating            | 15 A                |
| Voltage Rating Description | 125 V               |
| Phase                      | Single Phase        |
| Current / Amperage Rating  | 15 A                |
| Connectivity               | Back and Side Wired |
| Wattage                    | 1875 W              |
| Voltage Rating             | 125 VAC             |

### Dimensions

|            |                             |
|------------|-----------------------------|
| Length     | 3.28 in                     |
| Width      | 1.57 in                     |
| Weight     | 0.2 lb.                     |
| Height     | 1.15 in                     |
| Dimensions | 3.28 in x 1.57 in x 1.15 in |

### General

|                              |   |
|------------------------------|---|
| Series                       | Hubbell-Pro   |
| OEM Brand Name               | Hubbell Wiring Device-Kellems   |
| Style                        | Smooth Face   |
| Color                        | Light Almond  |
| Item Type                    | Traditional Duplex  |
| Material - Mounting Hardware | Screw Mounting  |
| Type                         | Receptacle  |
| Material                     | Nylon   |
| Specifications               | <ul style="list-style-type: none"> <li>• Automatic Self-grounding Staple - Stainless steel</li> <li>• Base - PBT</li> <li>• Clamping Plate - Plated steel</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Galvanized steel</li> <li>• Power Contacts - Brass</li> </ul> |
| UPC                          | 783585542157  |

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

### Operational

|                   |           |
|-------------------|-----------|
| Indicator(s) Type | Green LED |
|-------------------|-----------|

Operating Temperature

Maximum continuous 75°C and  
minimum -40°C without Impact

Horsepower - Maximum

0.5

### Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)



A Hubbell brand