

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Receptacles,
Duplex, Load Controlled, 15A 125V, 2-Pole
3-Wire Grounding, 5-15R, Back and Side
Wired, Blue**

By Hubbell Wiring Device-Kellems
Catalog # [BR15C2BL](#)

Straight Blade Devices, Receptacles, Duplex, Load Controlled,
15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Back and Side Wired,
Blue



Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

Application

Commercial Specification Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Nema Rating	5-15R
Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified 22.2, No. 42• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186

Conductor

Number Of Poles	2-Pole
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Current

Dielectric Strength	Withstands 2,000V minimum
Amperage Rating	15 A

Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Current Rating	15 A
Voltage Rating	125 V

Dimensions

Width	0.83 in
Height	3.28 in
Display Size	Standard Sized Product
Length	1.32 in
Dimensions	1.32 in x 0.83 in x 3.28 in

General

Item Type	Traditional Duplex
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Galvanized Steel• Mounting Strap - .040 in. (1) Galvanized steel• Power Contacts - .030 in. (.8) Brass• Terminal Screws - Plated steel• Wire Clamp - .062 in. (1.6) Nickel plated steel
Style	Smooth Face
Material	Nylon
Color	Blue

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.5

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)

