

Straight Blade Devices, Receptacles,
Decorator Duplex, Load Controlled, 15A
125V, 2-Pole 3-Wire Grounding, 5- 15R,
Back and Side Wired, Blue

By Hubbell Wiring Device-Kellems
Catalog # [DR15C2BL](#)

Straight Blade Devices, Receptacles, Decorator Duplex, Load
Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Back and
Side Wired, Blue

Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

Application

Commercial Specification Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Industry Standard(s)	• CSA Certified 22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG



Number Of Poles	2-Pole
Current	
Dielectric Strength	Withstands 2,000V minimum
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
Width	0.83 in
Height	3.28 in
Length	1.32 in
Dimensions	1.32 in x 0.83 in x 3.28 in

General

Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Type	Two Controlled Faces
Series	Controlled
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Nylon
Style	Style Line Decorator
Color	Blue

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)