

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Commercial Specification Grade Duplex
Receptacles for Controlled Applications



Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Patented TR design eliminates plug-in difficulty and TR complaints
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control system or other available energy management system

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Decorator face, back and side wired	Gray	783585582887	DR15C2GRYTR

Listings

Fed. Spec. W-C-596
NEMA® WD-6 Compliant
UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42

Online Resources

[eCatalog](#)



Specifications

Face	Nylon
Base	Nylon
Power Contacts	.030 in. (.8) Brass
Mounting Screws	Galvanized Steel
Wire Clamp	.062 in. (1.6) Nickel plated steel
Mounting Strap	.040 in. Galvanized steel
Ground Contacts	Brass
Automatic Self-grounding Staple	Stainless steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#12-10 AWG stranded or solid copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

