

## Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

# Commercial Specification Grade Duplex Receptacles for Controlled Applications

# HUBBELL

## Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Patented TR design eliminates plug-in difficulty and TR complaints
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control system or other available energy management system



## Ordering Information

| Description                         | Device Color | UPC Number   | Catalog Number |
|-------------------------------------|--------------|--------------|----------------|
| Decorator face, back and side wired | Brown        | 783585583051 | DR20C2TR       |

## Listings

Fed. Spec. W-C-596  
NEMA® WD-6 Compliant  
UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42

## Online Resources

[eCatalog](#)

## Specifications

|                                 |                                    |
|---------------------------------|------------------------------------|
| Face                            | Nylon                              |
| Base                            | Nylon                              |
| Power Contacts                  | .030 in. (.8) Brass                |
| Ground Contacts                 | Brass                              |
| Wire Clamp                      | .062 in. (1.6) Nickel plated steel |
| Mounting Strap                  | .040 in. Galvanized steel          |
| Automatic Self-grounding Staple | Stainless steel                    |
| Mounting Screws                 | Galvanized Steel                   |

## Performance

### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical

|                         |  |
|-------------------------|--|
| Product Identification  | Ratings are a permanent part of the device             |
| Terminal Accommodation  | #12-10 AWG stranded or solid copper wire only.         |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

### Environmental

|                       |   |
|-----------------------|---|
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (w/o impact) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

