

Switches, Double Pole  
20A, 120-277V AC  
Pre-Wired Style Line® Decorator Series  
Specification Grade Switch

Features

- Labor Saving
- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant

Ordering Information

| Description                                  | Rocker Color | UPC          | Catalog Number |
|----------------------------------------------|--------------|--------------|----------------|
| Rocker,<br>Polycarbonate,<br>Pre-wired leads | Almond       | 783585150932 | DSL220AL       |

Listings

UL Listed  
CSA Certified

Specifications

|                 |                                             |
|-----------------|---------------------------------------------|
| Contacts        | Silver Alloy                                |
| Terminal Screws | Brass                                       |
| Rocker Material | Thermoplastic                               |
| Mounting Bridge | Nickel Plated Steel with Auto Ground Staple |
| Contacts        | Silver Alloy                                |
| Ground Screw    | Brass (Green)                               |

Performance

|                         |                                                |
|-------------------------|------------------------------------------------|
| Electrical              |                                                |
| Dielectric Voltage      | Withstands 1500V AC minimum for 1 minute       |
| Max. Continuous Current | 20A                                            |
| Max. Working Voltage    | 277V AC                                        |
| Overload                | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise        | 30°C maximum at rated current                  |


Mechanical

Terminal Accommodations 8" #12 AWG THHN

Environmental

|                       |                                                              |
|-----------------------|--------------------------------------------------------------|
| Flammability          | UL 94V-2                                                     |
| Operating Temperature | Max. continuous: 75°C; Min. continuous: -40°C without impact |

HUBBELL



Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

