

Switches and Lighting Control, Decorator Switch Specification Grade, Rocker Switches, General Purpose AC, Illuminated Single Pole, 20A 120/277V AC

By Hubbell Wiring Device-Kellems
Catalog # [DS120ILR](#)

Switches and Lighting Control, Decorator Switch Specification Grade, Rocker Switches, General Purpose AC, Illuminated Single Pole, 20A 120/277V AC, Back and Side Wired, Red

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute, Electrical - Max. Continuous Current - 20A, Electrical - Max. Working Voltage - 277V AC, Electrical - Overload - Minimum 4.8 times rated current for 100 cycles, Electrical - Temperature Rise - 30°C maximum at rated current, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact, Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL Listed

Conductor

Wire Size	#14 AWG to #10 AWG
Number Of Poles	Single Pole

Current

Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Current Rating	20 A
Amperage Rating	20 A
Current / Amperage Rating	20 A
Connectivity	Back and Side Wired
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Dimensions

Length	4.28 in
--------	---------



Width	1.43 in
Weight	0.2 lb.
Height	1.54 in
Dimensions	4.28 in x 1.43 in x 1.54 in

General

Series	Illuminated
Style	Single Pole
Color	Red
Item Type	Single Pole Style Line Illuminated Decorator Switch Rocker/Decorator
Type	Thermoplastic
Material	
Specifications	

- Contacts - Silver Alloy
 - Contacts - Silver Alloy
 - Ground Screw - Brass (Green)
 - Mounting Bridge - Nickel Plated Steel with Auto Ground Staple
 - Rocker Material - Thermoplastic
 - Terminal Screws - Brass
- UPC 783585169934

UPC

Logistics

Carton Quantity	10
-----------------	----

Operational

Indicator	Light On with Load Off
Indicator(s) Type	Blue LED
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)