



Power Protection Products, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, With Nightlight, Almond

By Bryant
Catalog # [GFRST15ALNL](#)

Power Protection Products, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, With Nightlight, Almond

Features


- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction
- Includes light sensor controls for automatic on and off, custom dual lens for optimum light output

Specifications

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Current

Current / Amperage Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V



General

Type	Standard
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
UPC	883778123207
Style	Nightlight
Color	Almond

Logistics

Carton Quantity	10
-----------------	----