



Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond

By Bryant
Catalog # [GFTWRST15ALIG](#)

Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Specifications

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Current

Current / Amperage Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V

General

Type	Tamper-Resistant, Weather Resistant
------	-------------------------------------

Series Specifications

UPC
Style
Color

Heavy Duty

- Base - Nylon
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Zinc plated steel
- Power Contacts - Brass

883778122729
Isolated Ground
Almond

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)