

Replaced by HBL10P50ALU, Surge Arrestors, 40KA, 347/600V AC, Three Phase Y, Type 1

By Hubbell Wiring Device-Kellems
Catalog # [HBL10SA40](#)

Surge Arrestors, 40KA, 347/600V AC, ThreePhase Y, Type 1

Features

- 36,000, 40,000 and 50,000 Peak Amperage Capacity
- Surge arrestors are a low cost solution that may be installed on the line side or load side of the service entrance
- Excellent for OEM applications where size is an important variable
- Single phase wired-in surge protective devices feature a compact design

General

| | |
|-------------------|------------------------|
| Catalog Number | HBL10SA40 |
| EU RoHS Indicator | Contact Manufacturer |
| Series | Wired-In Surge Devices |
| Type | 40kA |



UPC 783585833156

Electrical Ratings

| | |
|----------------------------|-----------------|
| Voltage Rating | Wye 347/600 VAC |
| Voltage Rating Description | 347/600 VAC Wye |

Product Assets

[Catalog Page - WDK M-22 Catalog Page](#)
[Catalog Page - WDK M-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL10SA40 AutoCAD Drawing](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Specifications - HBL10SA40](#)
[Warranty - SPD Series: 36kA, 40kA & 80kA](#)