




Power Protection Devices, Receptacle, Self Test, GFCI, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Almond

By Bryant
Catalog # [GFTWRST20AL](#)

Power Protection Devices, Receptacle, Self Test, GFCI, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Almond



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Specifications

Industry Standard(s)	Meets All NEC® Requirements
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-20R

Current

Current / Amperage Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V

General

Type

Tamper-Resistant, Weather Resistant

Series

Heavy Duty

Specifications

- Base - Nylon
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Zinc plated steel
- Power Contacts - Brass

UPC

883778122644

Style

Standard

Color

Almond

Logistics

Carton Quantity 10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)