

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL1379D](#)

Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC



Features

- Optional Side Guard for close wall applications
- Switch can be locked in the off position
- Thermoset body provides resistance to electrical arc tracking

Application

Standard Toggle

Specifications

Industry Standard(s)	<ul style="list-style-type: none"> • CSA-C22.2 No.14 Industrial Control File LR-46186 • UL 508, Industrial Control File #E70402
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Current

Phase	Three Phase
Dielectric Strength	2,200V AC minimum for 1 minute
Connectivity	Pressure Terminal Screws
Current Rating	30 A
Amperage Rating	30 A
Wattage	18000 W

Dimensions

Width	3.2 in
Weight	1.05 lb.
Height	3.15 in
Length	4.52 in
Dimensions	4.52 in x 3.2 in x 3.15 in

Force Related

Load Capacity	Inductive
---------------	-----------

General

Material - Mounting Hardware	Screw Mounting
Type	Disconnect Switches
Specifications	Enclosure Material - Aluminum
UPC	783585202617
Style	Standard Duty

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Product Assets

[Catalog \[English\]](#)