

# Temporary Power

## Temporary Industrial Lighting

### LED Stringer Lights

#### Features

- Self Locking Connector
- Magnetic mounting bracket
- Bracket Adjustment Knobs
- Hanging hook
- For Wet Locations

#### Ordering Information

Description	UPC	Catalog Number
60 LEDs per fixture, 5 fixtures, light string with magnetic base included	783585580203	HBL182S50LEDH

#### Listings

UL  
CSA  
ETL

#### Specifications

Product Type	LED
Plug Type	NEMA 1-15P
Connector Type	NEMA 1-15R

#### Performance

Electrical	
Lamp Life	50,000 Hours
Lumen Output per Fixture, 5 Fixtures	5, 1,100 (5,500 total)
Rating	15A 120VAC 60Hz.
Watt per fixture	9.6

Mechanical	
Cord	18/2 18 AWG
Cord Length	50 ft. 18 AWG
Enclosure	Polycarbonate
Lens	Polycarbonate
Lens Gasket	Silicon
Mounting Bracket/Hanging Hook	Steel
Number of fixtures	5

# HUBBELL



#### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

